

Combination station vertical

Configuration

Front sash with distinct settings

Light curtain

VFR connection supply and exhaust air

Slack rope protection

Lighting

Pressure monitoring for pre-chamber and workspace

Pressure monitoring for workspace

Door monitoring lateral section

Integrated side shifter

Temperature control for lateral section

Temperature control for exhaust air

Signal lamp (LED) and acoustic signal

PLC control

Supply air filter acc. according IOS class

Optional features

Integrated hatch for the units

Plug in for heating plates

Underfloor flushing

Drumming station (diverse varieties)

Partition

Integrated computer and keyboard

Temperature control for workspace

Dropping

Spot suction

Plug ins for temperature control

Media supply acc. customer requirement

Remote maintenance acc. customer requirement

Operating device for media supply (hand, foot or panel)

Millipore

Distillery

Ultrasonic bath

Exhaust air scrubber and exhaust air irrigation



Contact & Support

MK Versuchsanlagen und Laborbedarf e.K.

Stueckweg 10 - 35325 Muecke-Merlau

Tel.: +49 6400-9576030

Fax: +49 6400-9576031

info@mk-versuchsanlagen.de

www.mk-versuchsanlagen.de

