

# Workstation vertical

## Configuration

Front sash with distinct settings

Light curtain

VFR connection supply and exhaust air

Slack rope protection

Lighting

Pressure monitoring for antechamber and workspace

Temperature control for exhaust air

Signal lamp (LED) and acoustic signal

PLC control

Supply air filter acc. according IOS class

## Optional features

Integrated hatch for the units

Plug in for heating plates

Underfloor flushing

Drumming station (diverse varieties)

Temperature control for workspace

Partition

Integrated computer and keyboard

Dropping

Spot suction

Plug ins for temperature control

Media supply acc. customer requirement

Remote maintenance acc. customer requirement

Operating device for media supply (hand, foot or panel)

Millipore

Distillery

Ultrasonic bath

Exhaust air scrubber and exhaust air irrigation



## Contact & Support

**MK Versuchsanlagen und Laborbedarf e.K.**

Stueckweg 10 - 35325 Muecke-Merlau

Tel.: +49 6400-9576030

Fax: +49 6400-9576031

info@mk-versuchsanlagen.de

www.mk-versuchsanlagen.de

